



IPC-T42EA

4MP H.265 Turret PoE Camera

T42EA delivers 4MP live monitoring with a choice of 2.8mm / 3.6 mm lens option, it supports the latest H.265 compression which can save up to 50% bandwidth and storage. Human Detection allows you to monitor what matters without receiving annoying false alerts.



H.265 4MP QHD

See more than 1080P



Human Detection

Quickly find human targets in you home



Built-in Microphone

High quality microphone picks up sounds clearly while monitoring



H.265 Codec

Save more high-quality video in less space



PoE

An Ethernet cable provide both data connection and electric power



Alarm Notification

Sends instant motion-activated alerts to your mobile phone



Diversified Storage

Supports NVR, Cloud Storage or Micro SD card (up to 256GB)



24/7 Protection

Infrared night vision for clear-as-day clarity even in pitch dark



Stay close with what you care

With Cloud service, you will have access to what you care as long as Internet is available. You can record daily or motion videos on Cloud and play back anytime anywhere.



Specifications

Camera

1/2.8" 4 Megapixel Progressive CMOS 4MP(2560 x 1440)

Night Vision: 30m(98ft) Distance 2.8mm/3.6mm Fixed Lens

Field of View: 2.8mm; 90° (H), 50° (V), 107° (D)

3.6mm: 76° (H), 40° (V), 92° (D)

Video & Audio

Video Compression : H.265/H.264 Up to 25/30 fps Frame Rate 8x Digital Zoom Built-in Mic

Notice Management

Motion Detection Configurable Region Human Detection

What's in the box

- 1x Camera
- 1x Screw Package
- 1x Quick Start Guide 1x Mounting Template
 - 1x Mounting Plate

Network

1 x 100Mbps Ethernet Port Imou App: iOS, Android ONVIF

Auxiliary Interface

Micro SD Card Slot (up to 256GB) Reset Button

General

Power Consumption:<3W Material: Plastic

Working Environment:-20° C~+50° C, Less Than 95%RH Dimensions: Φ 109.9mm \times 81.3mm (Φ 4.3 \times 3.2inch)

Weight: 180 g (0.40 lb)

CE, FCC,

