

FSP12-imou

Solar Panel for imou Cell 2 & Cell Go



Dimension	197mm *138mm*25mm (without bracket)
Encapsulation method	PET laminated
Solar silicon crystal	Single crystal
Open circuit voltage	7.4V (-5%/+10%)
Short circuit current	0.508A (-5%/+10%)
Solar panel working voltage	6.2V (-5%/+10%)
Working current	0.484A (-5%/+10%)
Solar panel power Max Power(Ppm)	3W (-5%/+10%)
Operating temperature	-20°C to +60°C
Storage conditions	Temperature -20°C~45°C,
	Humidity<60%
Conversion rates	18.2%±2%
Protection Level	IP65
Connection with camera	Micro USB