

# VIDAA SMART TV 24" (60cm)

## SRT24HE4203



DVB-T2/C/S2

NETFLIX

YouTube

prime video

Disney+



Smart TV



Image Quality Ratio 200



USB playback



Inbuilt Wi-Fi



Hotel mode



8 bit

## Great entertainment in a compact size

With its elegant design, the SRT24HE4203 VIDAA TV combines everything that makes watching TV today an experience for you and your family. The integrated speakers offer you the perfect sound experience for your home with Dolby Audio. Play your favourite music, photos and videos on your TV screen using the built-in USB port. A highlight is given by the access to the VIDAA platform, with apps like Netflix, YouTube, Primevideo and much more. You can even download your TV remote control to your smartphone. No more need for the physical remote control! Further apps can easily be selected for more entertainment. Besides that, this TV comes with a built-in DVB-T2/C/S2 tuner and CI slot. Experience television like never before.

- Built-in DVB-T2/C/S2 tuner
- CI slot for conditional access to Pay TV
- Smart TV: entertainment and information
- Netflix app: TV shows and movies, including Netflix original series\*
- Image Quality Ratio 200
- Wireless connection with built-in Wi-Fi®
- USB for playback
- Electronic Programme Guide (EPG)
- Share media or mirror the screen from a smartphone/tablet to the TV

### VIDAA SMART TV 24" (60cm) SRT24HE4203



SRT24HE4203

<b>PICTURE &amp; SOUND</b>	
Display Frequency	50/60 Hz
Display Resolution	1366 x 768 (HD)
Viewing angle	178/178 (typ.)
Panel brightness	150cd/m <sup>2</sup>
Image Quality Ratio (IQR)	200
Response time (in ms)	9.5
Contrast ratio	3000:1
Picture processing	3D
HDR	-
Sound Type	Stereo
Speakers	2 x 8 W
Colour bit depth	8
<b>RECEPTION</b>	
DVB-T2/HEVC H.265	✓
DVB-C*/MPEG-4	✓
DVB-S2/MPEG-4	✓
CI	✓
<b>USER CONVENIENCE</b>	
USB multimedia	✓
Built-in Wi-Fi	802.11 b/g/n
Wi-Fi Display	✓
Smartphone/Tablet remote support	✓
EPG**	✓
Favourite channel list	✓
Teletext	✓
Channel Editor	✓
Parental control	✓
Hotel Mode	✓
Sat: DiSEqC 1.0	✓
Sat: DiSEqC 1.2	✓
SatCR v1.0	✓
Subtitles	✓
Bluetooth	-
HbbTV version	2.0
Fast Scan	-
<b>INTERNET SERVICES</b>	
Smart TV version	VIDAA U4.1
Apps	Netflix, YouTube, Amazon and more
Web browser	✓
Video-on-demand (VoD)	✓
Games	-
Mobile control	✓
Screen mirroring	✓
<b>CONNECTIVITY</b>	
HDMI 1.4 (total)	3
HDMI 1.4 (ARC)	1
USB (total)	2
USB 2.0	2
AV in	✓
Headphones	✓
Ethernet (RJ-45)	✓
S/PDIF	coaxial
ANT in (IEC terrestrial/cable)	✓
SAT in (F Sat)	✓
CI slot	✓
<b>GENERAL DATA</b>	
Colour	Black
Screen size (cm/inch)	59.94 / 23.6
Bezel width in mm	12.9/12.9/12.9/17.5
Thickness in mm (without stand)	81
Size (WxDxH) in mm	550.7 x 161 x 367.3
Size (WxDxH) in mm (without stand)	550.7x81x325
Weight in kg	2.5
Weight without stand in kg	2.4
Packaging dimension (in mm)	610 x 130 x 400
Power Supply	100~240Volt AC
Power consumption working (typ./ max.)	28 W /40 W
Power consumption in standby	≤0.5W
Energy efficiency class	F
Fixed stand	✓
Wall mount VESA (not included) in mm	100 x 100
EAN	9120072374302

Available Languages: EN, DE, FR, IT, ES, PT, PL, CZ, SK, NL, BG, GR, HU, HR, SL, RO, RS, RU, UA

\* DVB-C is only available in certain countries and for certain operators. For certain operators, a subscription and conditional access are necessary. For more information, please contact your operator.

\*\*Availability depending on broadcast

Subject to alterations. In consequence of continuous research and development technical specifications, design and appearance of products may change.

Manufactured under license from Dolby Laboratories. Dolby, Dolby Audio and the double-D symbol are trademarks of Dolby Laboratories. The terms HDMI, HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Wi-Fi is a registered trademark of Wi-Fi Alliance<sup>®</sup>. Netflix is a registered trademark of Netflix, Inc. YouTube<sup>™</sup>

is a trademark of Google Inc. All product names are trademarks or registered trademarks of their respective owners.

© STRONG 2023. All rights reserved.

SERVICE CENTER			
AT	support_at@strong.tv 0800-400130 (K.Ö.2/Mit. Oster, Feiertag)	IT	support_it@strong.tv 197 404 032 Da sera, fino a 8 ore, al min. 2,5 cent. costo alla risposta. Da mercoledì a venerdì, al min. 15,0 cent. costo alla risposta.
BE	support_be@strong.tv +359 32 434541	ES	support_es@strong.tv +34 91 519 61 76
BG	support_bg@strong.tv 844 66 44 90	FR	support_fr@strong.tv +351 2 100 06 325
CZ	support_cz@strong.tv	GR	support_gr@strong.tv 803 702 017
DE	support_de@strong.tv 0800 503 49 91 (0-140 Uhr, Wochenende, Feiertag) (0-140 Uhr, max. 900 Minuten)	HR	support_hr@strong.tv +385 1 344 57 66
DK	support_dk@strong.tv	HU	support_hu@strong.tv 0800 15 05 50
EE	support_ee@strong.tv	IE	support_ie@strong.tv +34 91 519 61 76
ES	support_es@strong.tv	IT	support_it@strong.tv +351 2 100 06 325
FR	support_fr@strong.tv	PL	support_pl@strong.tv +36 1 445 26 30
GR	support_gr@strong.tv	PT	support_pt@strong.tv
HR	support_hr@strong.tv	RO	support_ro@strong.tv
HU	support_hu@strong.tv	RS	support_rs@strong.tv
IE	support_ie@strong.tv	RU	support_ru@strong.tv
IT	support_it@strong.tv	UA	support_ua@strong.tv
UK	support_uk@strong.tv		