REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCH 10/22/09'	~	LJC 10/22/09'
B	Drawing correction	JLZ 02/10/15'	~	



NOTES:

1. ELECTRICAL CHARACTERISTICS:
   - 1.1 CONTACT RESISTANCE: 20mΩ Max. INITIAL.
   - 1.2 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
   - 1.3 INSULATION RESISTANCE: 1000MΩ Min.
2. MECHANICAL CHARACTERISTICS:
   - 2.1 CONTACT RETENTION FORCE: 500gf Min.
3. ENVIRONMENT CHARACTERISTICS:
   - 3.1 TEMPERATURE RANGE: −40°C ~ +105°C.
4. PRODUCT NUMBER CODE:

DS1023− X X X X

- PROFILE HEIGHT(DIM A)
  - 1: 8.5mm
  - 2: 5.0mm
- CONTACT PLATING
  - F1: FULL GOLD FLASH
  - 2: NICKEL + GOLD FLASH
- MOUNTIING TYPE
  - S: Straight TYPE
- No.OF CONTACTS
  - 1*1−1*40
  - 2*2−2*40
  - 3*3−3*40

CONNFLY
Tel:86-574-63508787
Fax:86-574-63510817
E-mail:sale@connfly.com
http://www.connfly.com
Add:East Industry Zone KuangYan
Town Cixi Ningbo China
P.C:315333

GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°

DRAWING TYPE	CUSTOMER		
SCALE	1:1	SHEET	1 OF 1
DRAWING NO.	C-DS1023-XXX1-B		

PROJECTION		TITLE	FEMALT HEADER PITCH 2.54mm V/T SINGLE/DUAL ROWS TYPE
UNITS	mm		
SHEET SIZE	A4	SERIES	DS1023 SERIES

晨翔电子有限公司
CONNFLY ELECTRONIC CO. LTD