


REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCH 10/22/09'	~	LJC 10/22/09'
B	Drawing correction	JLZ 02/10/15'	~	

NOTES:

- ELECTRICAL CHARACTERISTICS:
  - CONTACT RESISTANCE: 20mΩ Max. INITIAL.
  - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
  - INSULATION RESISTANCE: 1000MΩ Min.
- MECHANICAL CHARACTERISTICS:
  - CONTACT RETENTION FORCE: 500gf Min.
- ENVIRONMENT CHARACTERISTICS:
  - TEMPERATURE RANGE: -40°C ~ +105°C.
- PRODUCT NUMBER CODE:

DS1023- X X X X

- PROFILE HEIGHT(DIM A)
  - 1: 8.5mm
  - 2: 5.0mm
- CONTACT PLATING
  - F1: FULL GOLD FLASH
  - 2: NICKEL + GOLD FLASH
- MOUNTING TYPE
  - S: Straight TYPE
- No.OF CONTACTS
  - 1\*1-1\*40
  - 2\*2-2\*40
  - 3\*3-3\*40



Tel: 86-574-63510817

Fax: 86-574-63510817

E-mail: sale@connfly.com

http://www.connfly.com

Add: East Industry Zone KuangYan

Town Cixi Ningbo China

P.C: 315333

GENERAL TOLERANCE	ANGLE TOLERANCE	PROJECTION		TITLE	FEMALT HEADER PITCH	
X. ±0.60	X. ±5°	UNITS	mm	2.54mm V/T SINGLE/DUAL ROWS TYPE		
.X ±0.38	.X ±3°	SHEET SIZE	A4	SERIES	DS1023 SERIES	
.XX ±0.25	.XX ±2°	晨翔电子有限公司 <b>CONNFLY CONNFLY ELECTRONIC CO. LTD</b>				
DRAWING TYPE	CUSTOMER					
SCALE	1:1					SHEET
DRAWING NO.	C-DS1023-XXX1-B					