

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	HP 21/06/05	~	LJC 21/06/05
B	整理图面	YCH 09/17/07	~	

NOTES:


1. SPECIFICATIONS

- . Contact Resistance: 30mΩ max
- . Insulation Resistance: 1000MΩ min.
- . Current Rating: 1A
- . Dielectric withstanding voltage: AC 500V For 1 minute
- . Contact: Copper alloy.
- . Housing: Thermoplastic(UL 94V-0)

2. PRODUCT NUMBER CODE:

DS1091 - X X X X

- Screw type
- X: W/O screw
- S: W/ #4-40(UNC) screw
- D: Rivet Type With Screw
- In Bulk Package
- Contact plating
- O: Selective gold flash
- Shell plating
- N: Nickel
- 6: Tin
- Color of housing
- W: WHITE
- B: BLACK
- V: Ivory



Screw

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	UNIT	TITLE
X.	±0.60	X.	±5°	mm		DVI PLUG WITH RIGHT
.X	±0.38	.X	±3°			ANGLE 24+5(JDR-245)
.XX	±0.25	.XX	±2°			
DRAWING TYPE		CUSTOMER		SHEET SIZE	A4	SERIES
SCALE		1:1	SHEET	1 OF 1		DS1091
DRAWING NO.		C-DS1091-XXXX				



晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD