




REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 09/28/05'	~	LJC 09/28/05'
B	ADD W/ Kink Figure	LL 11/04/06'	~	LJC 11/04/06'
C	ADD P/N Code	LJC 12/10/13'		

NOTES:


- ELECTRICAL CHARACTERISTICS:
 - CONTACT RESISTANCE: 20mΩ Max.
 - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
 - INSULATION RESISTANCE: 1000MΩ Min.
- ENVIRONMENT CHARACTERISTICS:
 - TEMPERATURE: -20°C~+105°C.
- PRODUCT NUMBER CODE:

DS1009 - X X X X X - X X X


- Packing Type(Box): ③
 - 2: 2 inner box/outer box
 - 4: 4 inner box/outer box
 - 6: 6 inner box/outer box
- Product Packing Type: ③
 - A: Tube + Plastic Nail
 - B: Tube + Rubber
 - C: Foam Board
- Housing Material: ③
 - 0: PBT UL94 V-0
 - 2: PBT UL94 HB
- Central support
 - S: W/ central support
 - X: W/O centralsupport
- Width(DIM D)
 - N: 7.62mm(06~28p)
 - W: 15.24mm(24~42p)
- Contact plating
 - T1: Tin
- Contact type
 - A: W/O kink
 - B: W/ kink
- No.OF CONTACTS
 - 06 08 14 16 18 20
 - 24 28 32 40 42



Position	Dimension			
	A	B	C	D
06	7.62	5.08	10.16	7.62
08	10.16	7.62	10.16	7.62
14	17.78	15.24	10.16	7.62
16	20.32	17.78	10.16	7.62
18	22.86	20.32	10.16	7.62
20	25.40	22.86	10.16	7.62
24	30.48	27.94	10.16	7.62
24	30.48	27.94	17.78	15.24
28	35.56	33.02	10.16	7.62
28	35.56	33.02	17.78	15.24
32	40.64	38.10	17.78	15.24
40	50.80	48.26	17.78	15.24
42	53.34	51.00	17.78	15.24



② W/ Kink Figure

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE	2.54mm IC SOCKET	
X.	±0.60	X.	±5°	UNITS	mm	Stamping Type	
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1009 SERIES
.XX	±0.25	.XX	±2°	 晨翔电子有限公司 CONNFLY ELECTRONIC CO., LTD			
DRAWING TYPE		CUSTOMER					
SCALE	1:1	SHEET	10F1				
DRAWING NO.		C-DS1009-XXXXX-XXX-C					