

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 09/28/05'	~	LJC 09/28/05'
B	ADD W/ Kink Figure	LL 11/04/06'	~	LJC 11/04/06'
C	ADD P/N Code	LJC 12/10/13'		

NOTES:

1. ELECTRICAL CHARACTERISTICS:

- 1.1 CONTACT RESISTANCE: 20mΩ Max.
- 1.2 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
- 1.3 INSULATION RESISTANCE: 1000MΩ Min.

2. ENVIRONMENT CHARACTERISTICS:

- 2.1 TEMPERATURE: -20°C~+105°C.

3. PRODUCT NUMBER CODE:

DS1009 - X X X X X - X X X

Packing Type(Box): ②
 2: 2 inner box/outer box
 4: 4 inner box/outer box
 6: 6 inner box/outer box

Product Packing Type: ③
 A: Tube + Plastic Nail
 B: Tube + Rubber
 C: Foam Board

Housing Material: ④
 0: PBT UL94 V-0
 2: PBT UL94 HB




Central support
 S: W/ central support
 X: W/O centralsupport

Width(DIM D)
 N: 7.62mm(06~28p)
 W: 15.24mm(24~42p)


Contact plating
 T1: Tin

Contact type
 A: W/O kink
 B: W/ kink

No.OF CONTACTS
 06 08 14 16 18 20
 24 28 32 40 42



Position	Dimension			
	A	B	C	D
06	7.62	5.08	10.16	7.62
08	10.16	7.62	10.16	7.62
14	17.78	15.24	10.16	7.62
16	20.32	17.78	10.16	7.62
18	22.86	20.32	10.16	7.62
20	25.40	22.86	10.16	7.62
24	30.48	27.94	10.16	7.62
24	30.48	27.94	17.78	15.24
28	35.56	33.02	10.16	7.62
28	35.56	33.02	17.78	15.24
32	40.64	38.10	17.78	15.24
40	50.80	48.26	17.78	15.24
42	53.34	51.00	17.78	15.24




Ⓑ W/ Kink Figure

GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°

DRAWING TYPE	CUSTOMER		
SCALE	1:1	SHEET	10F1
DRAWING NO.	C-DS1009-XXXXX-XXX-C		

PROJECTION	TITLE	2.54mm IC SOCKET	
UNITS	mm	Stamping Type	
SHEET SIZE	A4	SERIES	DS1009 SERIES

 晨翔电子有限公司
CONNFLY® CONNFLY ELECTRONIC CO., LTD

CONNFLY®
 Tel: 86-574-63511111
 Fax: 86-574-63511111
 E-mail: sale@connfly.com
 http://www.connfly.com
 Add: East Industrial Zone, KuangYan Town Cixi Ningbo China
 P.C: 315333