

**SPECIFICATION:**

Operating Voltage (Max.): 250 V  
 Operating Current (Nom.): 3 A  
 Operating Temperature: -25°C to 85°C  
 Insulation Resistance (Min.): 1000 MΩ  
 Contact Resistance (Max.): 20 mΩ  
 Dielectric Strength: 1,000 Vac

**MATERIAL:**





Material (Housing): nylon 66  
 Material (Terminal): brass, tin plated  
 Material (Contact Area): brass, tin plated

**HANDLING:**

Packaging: bulk

**TOLERANCE:**

.X: ± 0.25  
 .XX: ± 0.20



**Order Information**

Identifier:

**W33R**

Wafer series H33H pitch 2.5 mm single row angled

No. of Contacts:

#

2: 1 x 2

3: 1 x 3

4: 1 x 4

:

10: 1 x 10