

SPECIFICATION:

Operating Voltage (Max.): 250 V
 Operating Current (Nom.): 3 A
 Operating Temperature: -25°C to 85°C
 Insulation Resistance (Min.): 1000 MΩ
 Contact Resistance (Max.): 20 mΩ
 Dielectric Strength: 1,000 Vac

MATERIAL:






Material (Housing): nylon 66
 Material (Terminal): brass, tin plated
 Material (Contact Area): brass, tin plated

HANDLING:

Packaging: bulk

TOLERANCE:

.X: ± 0.25
 .XX: ± 0.20



Order Information

Identifier:

W33S

Wafer series H33H pitch 2.5 mm single row straight

No. of Contacts:

#

2: 1 x 2

3: 1 x 3

4: 1 x 4

:

10: 1 x 10