


REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	HP 06/10/05'		

NOTES:

- SPECIFICATIONS:
  - VOLTAGE RATING: 30V DC.
  - CONTACT CURRENT RATING: 1A MAX. PER PIN.
  - CONTACT RESISTANCE: 30 MILLIOHMS MAX.
  - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
  - INSULATION RESISTANCE: 1000 MEGAOHMS MIN.
  - OPERATING TEMPERATURE: -40°C~+105°C.

2. PRODUCT NUMBER CODE:

DS1093-01 - X X X X



Series No.  
DS1093-01

Tel:86-574-63508107




Fax:86-574-63510817

Email: info@connfly.com


Http://www.connfly.com

Address: Zone Kuang Yan

Town: Xixi Ningbo China



RECOMMEND PCB LAYOUT(TOLERANCE=±0.05)



GENERAL TOLERANCE	ANGLE TOLERANCE	PROJECTION	TITLE
X. ±0.60	X. ±5°	UNITS	MINI DIN 803 TYPE
.X ±0.38	.X ±3°	SHEET SIZE	SERIES DS1093-01 SERIES
.XX ±0.25	.XX ±2°		
DRAWING TYPE	CUSTOMER	<b>晨翔电子有限公司</b> <b>CONNFLY ELECTRONIC CO. LTD</b>	
SCALE	1:1 SHEET 1 OF 1		
DRAWING NO.	C-DS1093-01-XXXXX		