

10.1" IPS TOUCHSCREEN-LCD

Touchscreen display for professional installation



Our 10.1" IPS touch screen display has been specially developed for professional installation and offers an impressive range of technical specifications.

Its outstanding image quality and multiple connectivity options make it the ideal solution for a wide range of applications in industry, commerce and private projects.

MAIN FEATURES	
Special features	5-point touch screen Particularly high viewing angle Versatile connection options Separate speaker output Flexible power input
Display	10.1" (25.65 cm) IPS LCD
Resolution	1280 x 800 Pixels
Touch Specifications	Capacitive 5-point touch
Power supply	DC: 5 V - 24 V (Screw terminal) USB: 5 V 2 A
Connections	Power (Micro-USB) Touch (Micro-USB) HDMI Input VGA Input (via Mini-HDMI) Audio-Output (3,5 mm) Speaker (4 Ω / 3 W) Additional soldering points for display control

TECHNICAL SPECIFICATIONS	
Viewing angle	178°
Contrast	800:1
Brightness	350 cd/m ²
Backlight	LED
Operating temperature	-20 °C - 70 °C

ADDITIONAL INFORMATION	
Dimensions	286 x 198 x 26 mm
Article no.	RB-LCD10-3
EAN	4250236826097
Customs tariff no.	85249100

TECHNICAL DRAWING MOUNTING FRAME:





