



Spring flap for 3RW52 with cutout for HMI module Standard

|                                |                                     |
|--------------------------------|-------------------------------------|
| product brand name             | SIRIUS                              |
| product category               | Enclosure components                |
| product designation            | Hinged cover                        |
| design of the product          | With cutout for HMI module Standard |
| manufacturer's article number  |                                     |
| • of soft starter              | 3RW51                               |
| • of soft starter              | 3RW52                               |
| Substance Prohibittance (Date) | 02/15/2018                          |

|  |                |
|--|----------------|
| <b>Ambient conditions</b>                        |                |
| ambient temperature during storage and transport | -40 ... +80 °C |

|   |  |
|---|--|
| <b>Safety related data</b>                              |  |
| protection class IP on the front according to IEC 60529 | IP20   |
| touch protection on the front according to IEC 60529    | finger-safe, for vertical contact from the front |

|                                |                                |                           |                   |
|--------------------------------|--------------------------------|---------------------------|-------------------|
| <b>Certificates/ approvals</b> |                                |                           |                   |
| General Product Approval       | For use in hazardous locations | Declaration of Conformity | Test Certificates |

[Confirmation](#)



[Explosion Protection Certificate](#)



EG-Konf.



[Type Test Certificates/Test Report](#)

|                   |       |
|-------------------|-------|
| Marine / Shipping | other |
|-------------------|-------|



ABS



LRS



PRS



DNV-GS

[Confirmation](#)

**Further information**

Siemens has decided to exit the Russian market (see here).  
<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.  
 Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5950-0GL40>

Cax online generator  
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5950-0GL40>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3RW5950-0GL40>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RW5950-0GL40&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5950-0GL40&lang=en)

**Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current**

<https://support.industry.siemens.com/cs/ww/en/ps/3RW5950-0GL40/char>

**Characteristic: Installation altitude**

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5950-0GL40&objecttype=14&gridview=view1>

**Simulation Tool for Soft Starters (STS)**

<https://support.industry.siemens.com/cs/ww/en/view/101494917>

---

last modified:

12/15/2020 

