



Accessory for 3NJ62/63 Switch disconnecter with fuses In-line design, plug-in, NH1 current transformer 200/5 A, Cl. 0.5, legal-for-trade calibrated Bushing opening 15,2mm

Model		
product brand name	SETRON	
product designation	Current transformer	
design of the product	accessory for switch disconnecter with fuses 3NJ6	
Protection class		
protection class IP	IP20	
Mechanical Design		
height	65 mm	
width	44 mm	
depth	48 mm	
diameter of inlet opening	14 mm	
net weight	169 g	
Environmental conditions		
ambient temperature during operation		
• minimum	-10 °C	
• maximum	55 °C	
General Product Approval	Declaration of Conformity	other

[Confirmation](#)



[Miscellaneous](#)

[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NJ6930-3BF23>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NJ6930-3BF23>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NJ6930-3BF23

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

12/18/2020 

