

SENTRON, cylindrical fuse link, 10 x 38 mm, 10 A, gPV, Un DC: 1000 V



Model	
product brand name	SENTRON
product designation	Cylindrical fuse link
General technical data	
operating class of the fuse link	gPV
size of the fuse link	10x38 mm
type of voltage of the operating voltage	DC
supply voltage at DC	1 000 V
Main circuit	
operational current rated value	10 A
Product details	
product component striker	No
Mechanical Design	
mounting position	Any, preferably vertical
net weight	8 g
General Product Approval	
Declaration of Conformity	
other	

[Confirmation](#)



[Confirmation](#)

[Miscellaneous](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW6003-4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW6003-4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6003-4

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

2/17/2023 

