

## 300pcs Non-Insulated Cable Ferrules assortment- mini kit set, 0.75mm<sup>2</sup> / 1.0mm<sup>2</sup> / 1.5mm<sup>2</sup> / 2.5mm<sup>2</sup> Typ.2010C391



Material: Tinned Copper  
Working Temperature: 120°C max.  
Rating voltage: 600 V/AC max.



Wire range	Diameter Dø	Diameter dø	Length	contents
0.75 mm <sup>2</sup>	1.8 mm	1.1 mm	8 mm	100pcs
1.0 mm <sup>2</sup>	2.3 mm	1.4 mm	8 mm	100pcs
1.5 mm <sup>2</sup>	2.4 mm	1.7 mm	8 mm	50pcs
2.5 mm <sup>2</sup>	3.1 mm	2.2 mm	8 mm	50pcs