



135pcs Non-Insulated Cable Ferrules assortment- mini kit set, 4.0mm² / 6.0mm² / 10mm² / 16mm²

Typ.2010C393



Material: Tinned Copper
Working Temperature: 120°C max.
Rating voltage: 600 V/AC max.



Wire range	Diameter D \varnothing	Diameter d \varnothing	Length	contents
4.0 mm ²	4.0 mm	2.8 mm	10 mm	50pcs
6.0 mm ²	4.7 mm	3.5 mm	12 mm	50pcs
10 mm ²	5.6 mm	4.5 mm	12 mm	25pcs
16 mm ²	6.9 mm	5.8 mm	12 mm	10pcs