

## **TECHNICAL DATA SHEET**

www.quadrios.de

## CU-Wire LIY (Red, Black) Item-No.: 23CW020 ... 23CW025









Whether in the laboratory, workshops, development offices or even for hobby, leisure and education: with this high-quality copper stranded wire you are always well equipped. The PVC sheathing covers the high purity copper braid and ensures good dielectric strength and immediate differentiation of the cables. It is high purity copper with excellent solderability, making it the optimal solution for many applications. The solid PVC jacket can be easily removed.

**Technical data:** Material: PVC insulation, copper wire • Rated voltage: 230 V AC/DC • Operating temperature range: -30 ... +70 °C • Lead-free • Halogen-free • RoHS-compliant • Colors on spool: Red or Black.

Part No.	GTIN	Color / Content	Cross section	Structure CU wire	Outer diameter
23CW020	4260732282990	Red / 50 m	0.14 mm <sup>2</sup>	18 x 0.1 mm	1.2 mm
23CW021	4260732283003	Black / 50 m	0.14 mm <sup>2</sup>	18 x 0.1 mm	1.2 mm
23CW022	4260732283010	Red / 50 m	0.25 mm <sup>2</sup>	50 x 0.08 mm	1.4 mm
23CW023	4260732283027	Black / 50 m	0.25 mm <sup>2</sup>	50 x 0.08 mm	1.4 mm
23CW024	4260732283034	Red / 25 m	0.50 mm <sup>2</sup>	100 x 0.08 mm	2.0 mm
23CW025	4260732283041	Black / 25 m	0.50 mm <sup>2</sup>	100 x 0.08 mm	2.0 mm