

Article No. : 1FK2203-4AG00-2SA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Basic motor data	
Motor type	Permanent-magnet synchronous motor, Natural cooling, IP64
Motor type	Compact
Static torque	1.27 Nm
Static current	2.5 A
Maximum torque	3.75 Nm
Maximum current	7.8 A
Maximum speed	7,800 rpm
Rotor moment of inertia	0.3500 kgcm ²
Weight	1.5 kg

Rated data	
SINAMICS S210, 1AC 230V	
Rated speed	3,000 rpm
Rated torque	1.27 Nm
Rated current	2.5 A
Rated power	0.40 kW

Encoder system	
Encoder system	Encoder AS22DQC: Absolute encoder single turn 22 bit

Motor connection	
Connection type	OCC for S210
Connector size	M12

Mechanical data	
Design acc. to Code I	IM B5 (IM V1, IM V3)
Vibration severity grade	Grade A
Shaft height	30
Flange size (AB)	60 mm
Centering ring (N)	50 mm
Hole circle (M)	70 mm
Screw-on hole (S)	5.5 mm
Overall length (LB)	123 mm
Diameter of shaft (D)	11 mm
Length of shaft (E)	23 mm
Length of flange diagonal (P)	81 mm
Shaft end	Plain shaft
Color of the housing	Standard (Anthracite, similar to RAL 7016)

