

SIWAREX WP231 calibratable weighing electronic (1 channel) for strain gauge load cells / full bridges (1-4 mV/V) for SIMATIC S7-1200 or stand alone, RS485 and Ethernet-Interface, onboard I/O: 4 DI / 4 DO, 1 AO (0/4...20mA), attention: for calibratable applications please follow the local laws applying in the country of verification! Detailed load cell diagnostics possible with digital junction box SIWAREX DB (7MH5001-0AD20 or 7MH5001-0AD01).

### Further information

Industry Online Support (Manuals, Catalogs, Certificates, FAQ, ...)

<https://support.industry.siemens.com/cs/products?mf=ps&lc=en-WW>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>

