



SIMATIC ET 200SP HA, Terminal block, type K0, 16 push-in terminals, width: 22.5 mm,

Figure similar

General information	
Product type designation	Type K0
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; Asset data
Supply voltage	
Rated value (DC)	24 V
Current carrying capacity	
up to 70 °C, max.	10 A; Permitted load current of the potential group depending on the number of terminal blocks
For process terminals, max.	5 A
Hardware configuration	
Formation of potential groups	
<ul style="list-style-type: none"> support of potential groups 	Yes
<ul style="list-style-type: none"> New potential group 	No
<ul style="list-style-type: none"> Potential group continued from the left 	Yes
Slots	
<ul style="list-style-type: none"> Number of slots 	1
Potential separation	
between backplane bus and supply voltage	Yes; 4 200 V DC/1 min, type test
between potential groups (power bus)	Yes; 1 500 V DC/1 min, type test (SELV / PELV to functional ground FE)
between process terminals and supply voltage	Yes; 4 200 V DC/1 min, type test
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> horizontal installation, min. 	-40 °C
<ul style="list-style-type: none"> horizontal installation, max. 	70 °C
<ul style="list-style-type: none"> vertical installation, min. 	-40 °C
<ul style="list-style-type: none"> vertical installation, max. 	60 °C
Dimensions	
Width	22.5 mm
Height	175 mm
Depth	77 mm
Weights	
Weight, approx.	78 g
last modified:	8/8/2022