SIEMENS

Data sheet

6AG4025-0CB20-2BB0



SIMATIC IPC527G (Box PC); Core i5-6500 (4C/4T, 3.2 (3.6) GHz); 1 TB HDD, internal; 8 GB DDR4; Windows 7 Ultimate 64-bit, MUI; 2x Gigabit Ethernet (IE/PN); 1x DisplayPort, 1x VGA; 4x USB 3.0, 2x USB 2.0; 2x RS232/485/422 (can be selected); 2x RS232, 1x 8 bit DIO, 2x PCI; 1x PCIe x16, 1x PCIe x1; 100/240 V AC power supply without line cable

Installation type/mounting	
Mounting	Wall mounting, portrait mounting, desktop mounting
Design	Box PC, built-in unit
Supply voltage	
Type of supply voltage	100/240V AC (autorange) 50/60 Hz
Line frequency	
Rated value 50 Hz	Yes
 Rated value 60 Hz 	Yes
Processor	
Processor type	Core i5-6500 (4C/4T, 3.2 (3.6) GHz, 6 MB Cache)
Chipset	Intel H110
Graphic	
Graphics controller	Onboard Intel HD graphics 530/510 integrated in processor
Drives	
Hard disk	1 TB HDD
Memory	
Type of memory	DDR4-2666 SO-DIMM
Main memory	8 GB RAM
Capacity of main memory, max.	32 Gbyte
Hardware configuration	
Slots	
• free slots	1x PCIe (x16), 1x PCIe (x1), 2x PCI
 Number of PCI slots 	2
 Number of PCI slots 	2
Interfaces	
Number of industrial Ethernet interfaces	2; 2x Gigabit Ethernet (IE/PN), RJ45
Number of PROFINET interfaces	2
USB port	4x USB 3.0, 1x USB 2.0 internal, 2x USB 2.0 optional
Connection for keyboard/mouse	USB / USB
serial interface	2x RS 232 / 485 / 422, 2x RS 232
Multimedia	
Audio In/Out	Yes
Microphone In	Yes
Video interfaces	
Graphics interface	1x DisplayPort, 1x VGA
Industrial Ethernet	
 Industrial Ethernet interface 	2x Ethernet (RJ45)
— 100 Mbps	Yes
— 1000 Mbps	Yes
Integrated Functions	

Monitoring functions		
Status LEDs	POWER, HDD	
EMC		
Interference immunity against discharge of static electricity		
 Interference immunity against discharge of static electricity 	±6 kV contact discharge acc. to IEC 61000-4-2; ±8 kV air discharge acc. to IEC 61000-4-2	
Degree and class of protection		
IP degree of protection	IP20	
IP (at the front)	IP20	
IP (rear)	IP20	
Standards, approvals, certificates		
CE mark	Yes	
CSA approval	Yes; No. 61010-1-12, No. 61010-2-201	
UL approval	Yes	
cULus	Yes; UL 61010-1, UL 61010-2-201	
RCM (formerly C-TICK)	Yes	
KC approval	Yes	
EAC (formerly Gost-R)	Yes	
FCC	Yes	
Ambient conditions		
Ambient temperature during operation		
min.	0 °C	
• max.	40 °C	
Ambient temperature during storage/transportation		
• min.	-20 °C	
• max.	60 °C	
Relative humidity		
Relative humidity	8 85 % at 30 °C, no condensation	
Vibrations		
 Vibration resistance during operation acc. to IEC 60068- 2-6 	IEC 60068-2-6; 10 Hz to 58 Hz 0.015 mm; 58 Hz to 200Hz 1.96 m/s2	
Shock testing		
Shock load during operation	Tested in accordance with IEC 60068-2-27: With SSD: 150 m/s², 11 ms; with HDD: 9.8 m/s², 20 ms	
Operating systems		
pre-installed operating system	Windows 7 Ultimate (Multi-Language) 64-bit	
Additional info on operating system	Multi-Language User Interface (MUI): 5 languages (English, German, French, Spanish, Italian)	
pre-installed operating system		
Windows 7	Yes; Ultimate 64 bit	
Dimensions		
Width	260 mm	
Height	135 mm	
Depth	225 mm	

last modified:

5/31/2021