

SIMATIC ITC1500 V3, Industrial Thin Client, 15" widescreen TFT display, capacitive touch sensor, Supported protocols: RDP, VNC, SMARTSERVER HTML5 et. al., Neutral Design, panel mount



Figure similar

General information	
Product type designation	ITC1500 V3
Display	
Design of display	TFT widescreen display, LED backlighting
Screen diagonal	15.6 in; 15"
Display width	344.2 mm
Display height	193.5 mm
Number of colors	16 777 216
Resolution (pixels)	
• Image resolution	1 366 x 768
• Horizontal image resolution	1 366 pixel
• Vertical image resolution	768 pixel
General features	
• non-reflective and tempered mineral glass screen	Yes
• Detachable from computer unit	100 m
Backlighting	
• Type of backlighting	LED, dimmable
• MTBF backlighting (at 25 °C)	50 000 h; At 25°C
• Backlight dimmable	Yes
Control elements	
Control elements	multi-touch screen
Touch operation	
• Design as touch screen	Yes
• Design as multi-touch screen	Yes; Projective-capacitive
• Monitor keyboard	Yes
Installation type/mounting	
Design	Built-in unit
Front mounting	Yes
Support arm mounting	No
Stand mounting	No
Built-in unit	Yes
maximum permitted forward tilt angle from vertical	35°
maximum permitted backward tilt angle from vertical	35°
Supply voltage	
Type of supply voltage	DC
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Input current	

Current consumption (rated value)	1.4 A
Starting current inrush I <sup>2</sup> t	0.5 A <sup>2</sup> ·s
<b>Power</b>	
Active power input, typ.	34 W
<b>Power loss</b>	
Power loss, typ.	34 W
<b>Interfaces</b>	
Number of industrial Ethernet interfaces	2; 2 ports (switch)
Number of USB interfaces	4; on rear
USB on the rear	Yes; 2x onboard
Connection for keyboard/mouse	USB
<b>Industrial Ethernet</b>	
• Transmission rate, max.	1 000 Mbit/s
<b>Protocols</b>	
<b>Protocols (Ethernet)</b>	
• TCP/IP	Yes
• DHCP	Yes
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
<b>WEB characteristics</b>	
• HTTP	Yes
• HTML	Yes; HTML5
• XML	Yes
• CSS	Yes
• JavaScript	Yes
<b>Protocols (terminal link)</b>	
• Sm@rtServer	Yes
• RDP	Yes
• VNC viewer	Yes
• Citrix	No
• SINUMERIK	No
<b>Degree and class of protection</b>	
IP (at the front)	IP65
IP (rear)	IP20
<b>NEMA (front)</b>	
• Enclosure Type 4 at the front	Yes
• Enclosure Type 4x at the front	Yes
• Enclosure Type 12 at the front	Yes
<b>Standards, approvals, certificates</b>	
CE mark	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
<b>Use in hazardous areas</b>	
• ATEX Zone 2	Yes
• ATEX Zone 22	Yes
• IECEx Zone 2	Yes
• IECEx Zone 22	Yes
• cULus Class I Zone 2, Division 2	Yes
• FM Class I Division 2	Yes
<b>Marine approval</b>	
• Germanischer Lloyd (GL)	No; Available soon
• American Bureau of Shipping (ABS)	No; Available soon
• Bureau Veritas (BV)	No; Available soon
• Det Norske Veritas (DNV)	No; Available soon
• Lloyds Register of Shipping (LRS)	No; Available soon
• Nippon Kaiji Kyokai (Class NK)	No; Available soon
<b>Ambient conditions</b>	

<b>Ambient temperature during operation</b>	
• min.	0 °C
• max.	50 °C
<b>Ambient temperature during storage/transportation</b>	
• min.	-20 °C
• max.	60 °C
<b>Relative humidity</b>	
• Operation, max.	90 %; no condensation
<b>Vibrations</b>	
• Vibration load in operation	10 m/s <sup>2</sup>
• Vibration load during transport/storage	10 m/s <sup>2</sup>
<b>Shock testing</b>	
• Shock load during operation	150 m/s <sup>2</sup>
• shock acceleration during storage/transport	150 m/s <sup>2</sup>
<b>Software</b>	
Web browser	Yes; HTML5, CSS
<b>configuration / header</b>	
<b>Configuration</b>	
• Remote	Yes; Via web page
<b>Languages</b>	
<b>Online languages</b>	
• Number of online/runtime languages	3; german / english
<b>Peripherals/Options</b>	
USB memory	Yes; USB storage medium can be connected
<b>Mechanics/material</b>	
<b>Enclosure material (front)</b>	
• Aluminum	Yes
<b>Dimensions</b>	
Width of the housing front	398 mm
Height of housing front	257 mm
Mounting cutout, width	382 mm
Mounting cutout, height	241 mm
Overall depth	73 mm
<b>Weights</b>	
Weight (without packaging)	5 kg

**last modified:** 1/16/2021 