

SIMATIC IPC 477E 22" Multitouch (1920 x 1080); neutral front; 4 USB (back), Ethernet (10/100/1000); Core i3-6102E; 3x Gigabit Ethernet (IE/PN); Memory configuration: 4 GB; w/o RS232/RS485; w/o PCIe; Windows7 Ultimate SP1, 64 bit, MUI (ge, en, es, fr, it); w/o replaceable mass storage; Internal mass storage: 240 GB Solid-State Drive SATA; w/o SIMATIC Software; 24 V DC industrial power supply



Figure similar

Supply voltage	
Type of supply voltage	24 V DC
Processor	
Processor type	Core i3-6102E
Drives	
Hard disk	500 GB HDD
Memory	
Capacity of main memory, max.	4 Gbyte
Hardware configuration	
Slots	
• Number of PCI slots	0
Interfaces	
Number of industrial Ethernet interfaces	3
Number of PROFINET interfaces	3
Video interfaces	
• Graphics interface	1x DisplayPort, 1x VGA
Degree and class of protection	
IP (at the front)	IP65
Standards, approvals, certificates	
CE mark	Yes
UL approval	Yes
cULus	Yes
RCM (formerly C-TICK)	Yes
EAC (formerly Gost-R)	Yes
FCC	Yes
Dust protection	Protection against foreign bodies > 1 mm
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	45 °C
Operating systems	
pre-installed operating system	Windows 7 Ultimate (Multi-Language) 64-bit
pre-installed operating system	
• Windows 10 Enterprise	Yes; Windows 10 IoT Enterprise 2016 LTSC, 64bit, MUI
Dimensions	
Width	529 mm
Height	331 mm
Depth	85 mm
last modified:	10/30/2021

