

cable D-SUB/end sleeve shielded 8m

connection cable shielded f. SIMATIC ET200 SP HA from 37-pole D-sub to bare ends w. wire end sleeve labeled 32 channels L = 8 m, 0.14mm<sup>2</sup>



target system	SIMATIC ET 200SP HA
suitability for use	I/O modules
product type designation	Modular connection
product designation	Pre-assembled round cable
<b>Operating data / header</b>	
operating voltage / at DC	
• rated value	24 V
• maximum	60 V
ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-30 ... +70 °C
<b>General data / header</b>	
suitability for interaction	
• input card PLC	Yes
• PLC output card	Yes
suitability for use	
• digital signal transmission	Yes
• analog signal transmission	Yes
<b>Product properties, functions, components / general / header</b>	
number of channels	32
design of cable	Round cable
wire length	8 m
number of poles	32
number of conductors / of connection cable	32
conductor cross section / rated value	0.14 mm <sup>2</sup>
color / of cable sheath	Black
outer diameter / of cable sheath	9 mm
material / of the connection cable sheath	PVC
design of the shield	braided shield
connector type	D-Sub connector
type of electrical connection / on enclosure	Female header
number of poles / at the 1st interface	37; control page
type of electrical connection / in the field	End sleeve
number of poles / at the 2nd interface	32; numbered
certificate of suitability / cULus approval	No
reference code / according to IEC 81346-2	WG
net weight	1.25 kg
<b>last modified:</b>	7/13/2022 