



Figure similar

MLFB-Ordering data

6SL3210-5FB11-0UA1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Ambient conditions	
Input		Cooling	Fan
Number of phases	3 AC	Installation altitude	1000 m
Line voltage	200 ... 240 V +10 % -15 %	Ambient temperature	
Line frequency	45 ... 66 Hz	Operation	0 ... 45 °C
Output		Storage	-40 ... 70 °C
Rated power	1.00 kW	Relative humidity	
Rated current (IN)	6.30 A	Max. operation	90 %
Max. output current	18.90 A	Standards	
Inputs / outputs		Compliance with standards	CE, KC, cULus, EAC, C-Tick (RCM)

Standard digital inputs

Number	10
--------	----

Digital outputs

Number	6
--------	---

Analog inputs

Number	2
--------	---

Analog outputs

Number	2
--------	---

Mechanical data	
Degree of protection	IP20 / UL open type
Frame size	FSD
Net weight	2.35 kg
Width	95.0 mm
Height	170.0 mm
Depth	195.0 mm