

SIEMENS

Data sheet for SINAMICS V90



Figure similar

MLFB-Ordering data 6SL3210-5FE15-0UF0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data		Ambient conditions	
Input		Cooling	Fan
Number of phases	3 AC	Installation altitude	1000 m
Line voltage	380 ... 480 V +10 % -15 %	Ambient temperature	
Line frequency	45 ... 66 Hz	Operation	0 ... 45 °C
Output		Storage	-40 ... 70 °C
Rated power	5.00 kW	Relative humidity	
Rated current (IN)	12.60 A	Max. operation	90 %
Max. output current	37.80 A	Standards	
Inputs / outputs		Compliance with standards	CE, KC, cULus, EAC, C-Tick (RCM)

Standard digital inputs	
Number	4
Digital outputs	
Number	2

Mechanical data	
Degree of protection	IP20 / UL open type
Frame size	FSC
Net weight	5.65 kg
Width	140.0 mm
Height	260.0 mm
Depth	240.0 mm