

product type designation

product description

Plug-in cable RS422, M12/M12

Communication cable (6-core)

ASM adapter cable for MV500 for connection of MV500 to communications modules (CM) (M12 12-pole socket MV side - M12 8-pole connector CM side) length: 5 m.



suitability for use

Plug-in cable for connecting an MV500 reader to a communication module

wire length

5 m

electrical data

number of electrical connections

2

type of electrical connection

M12 (male, 8-pin, straight) / M12 (female, 12-pin, angled)

mechanical data

number of electrical cores

6

ambient conditions

ambient temperature

- during operation -25 ... +70 °C
- during storage -25 ... +70 °C
- during transport -25 ... +70 °C
- during installation -5 ... +70 °C

standards, specifications, approvals

reference code

- according to IEC 81346-2 WG
- according to IEC 81346-2:2019 WGB

further information / internet links

internet link

- to web page: selection aid TIA Selection Tool <https://support.industry.siemens.com/cs/ww/en/view/67384964>
- to website: Industrial communication <http://www.siemens.com/ident/rfid>
- to website: Industry Mall <https://mall.industry.siemens.com>
- to website: Information and Download Center <http://www.siemens.com/industry/infocenter>
- to website: Image database <http://automation.siemens.com/bilddb>
- to website: CAX-Download-Manager <http://www.siemens.com/cax>
- to website: Industry Online Support <https://support.industry.siemens.com>

last modified:

2/9/2022