

product type designation

product description

Plug-in cable, USB (Type A) / board connector

Standard cable for USB

SIMATIC RF1000 USB connecting cable for RF1000 reader Length 0.5 m;



Figure similar

suitability for use	short plug-in cable for connecting an RF1000 reader to the PC
wire length	0.5 m
electrical data	
number of electrical connections	2
type of electrical connection	USB connector (type A) / wire-to-board connector
mechanical data	
number of electrical cores	4
ambient conditions	
ambient temperature	
• during operation	-25 ... +55 °C
• during storage	-25 ... +55 °C
• during transport	-25 ... +55 °C
• during installation	-25 ... +55 °C
standards, specifications, approvals	
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	https://support.industry.siemens.com/cs/ww/en/view/67384964
• to website: Industrial communication	http://www.siemens.com/ident/rfid
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
last modified:	10/30/2021