


SIVACON S4 mounting plate 3VA10 (100A), 3-pole, fixed-mounted, plug-in socket, H:350mm W:800mm



Model	
product brand name	SIVACON S4
product designation	3VA mounting plate
design of the product	3VA10 (100 A); 3VA11 (up to 160 A)
design of the surface	galvanized
Appearance	
RAL color number	other
color	miscellaneous
Product details	
product component top plate	No
Mechanical Design	
height	350 mm
width	800 mm
depth	400 mm
length	800 mm
material thickness of the plate	2 mm
net weight	5 kg
material	metal
General Product Approval	Declaration of Conformity

[Confirmation](#)



[Miscellaneous](#)



Declaration of Conformity	Marine / Shipping	other	Environment	
		Miscellaneous	Confirmation	Environmental Confirmations

Further information

Siemens has decided to exit the Russian market (see here).
<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.
 Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ6000-8BA47>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ6000-8BA47>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ6000-8BA47

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/20/2023 

