

Data sheet for Line filter

Article No. : 6SL3203-0BE21-2VA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Rated data

Input

Number of phases	3 AC
Line voltage	200 ... 480 V

Output

Rated current	12.0 A
---------------	--------

Mechanical data

Degree of protection	IP20 / UL open type
Net weight	1.92 kg (4.23 lb)

Dimensions

Width	75.0 mm (2.95 in)
Height	170.0 mm (6.69 in)
Depth	140.0 mm (5.51 in)

Connections

Line side

Version	screw-type terminal
Conductor cross-section	0.25 ... 10.00 mm ² (AWG 24 ... AWG 8)

Load side

Version	Screw-type terminals
Cable length	20.00 m (65.62 ft)

PE connection

Version	On housing with M6 screw studs
---------	--------------------------------