

Data sheet for Line filter

Article No. : 6SL3203-0BE22-0VA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

[Figure similar](#)



Rated data	
Input	
Number of phases	3 AC
Line voltage	380 ... 480 V
Output	
Rated current	20.0 A
Mechanical data	
Degree of protection	IP20 / UL open type
Net weight	2.36 kg (5.20 lb)
Dimensions	
Width	60.0 mm (2.36 in)
Height	250.0 mm (9.84 in)
Depth	130.0 mm (5.12 in)

Connections	
Line side	
Version	screw-type terminal
Conductor cross-section	0.25 ... 10.00 mm² (AWG 24 ... AWG 8)
Load side	
Version	Screw-type terminals
Cable length	20.00 m (65.62 ft)
PE connection	
Version	On housing with M6 screw studs