

Data sheet for Line filter

Article No. : 6SL3203-0BE17-7BA1

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Rated data	
Input	
Number of phases	3 AC
Line voltage	380 ... 480 V
Output	
Rated current	11.4 A
Mechanical data	
Degree of protection	IP20 / UL open type
Net weight	1.75 kg (3.86 lb)
Dimensions	
Width	73.0 mm (9.35 in)
Height	237.5 mm (7.95 in)
Depth	65.0 mm (2.56 in)

Connections	
Line side	
Version	screw-type terminal
Conductor cross-section	1.00 ... 2.50 mm² (AWG 18 ... AWG 14)
Load side	
Version	shielded lead
Conductor cross-section	1.50 mm² (AWG 16)
Cable length	0.45 m (1.48 ft)
PE connection	
Version	On housing with M5 screw studs