



Figure similar

Data sheet for braking resistor

Article No. : 6SL3501-1BE32-0AA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Rated power P_{DB}	0.2 kW
Rated power, max.	1.2 kW

General technical specifications

Resistance	210 Ω
------------	--------------

Mechanical data

Degree of protection	IP65 / UL type 1
Net weight	1.56 kg (3.44 lb)
Dimensions	
Width	106 mm (4.17 in)
Height	320 mm (12.60 in)
Depth	64 mm (2.52 in)

Standards

Compliance with standards	CE, UL, cULus
---------------------------	---------------

Connections

Power connection	
Version	shielded lead
Cable length	1.8 m (5.91 ft)

Environmental conditions

Cooling method	natural convection
Ambient temperature in operation	-30 ... 55 °C (-22 ... 131 °F)