



Figure similar

Data sheet for braking resistor

Article No. : 6SL3501-1BE32-4AA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data	
Rated power P _{DB}	0.24 kW
Rated power, max.	1.44 kW

General technical specifications	
Resistance	220 Ω

Mechanical data	
Degree of protection	IP65 / UL type 1
Net weight	2.1 kg (4.63 lb)
Dimensions	
Width	106 mm (4.17 in)
Height	320 mm (12.60 in)
Depth	64 mm (2.52 in)

Standards	
Compliance with standards	CE, UL, cULus

Connections	
Power connection	
Version	shielded lead
Cable length	1.8 m (5.91 ft)

Environmental conditions	
Cooling method	natural convection
Ambient temperature in operation	-30 ... 55 °C (-22 ... 131 °F)