

Data sheet for braking resistor

Article No. : 6SL3501-1BE41-2CA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Rated data

Rated power P _{DB}	1.2 kW
Rated power, max.	7.2 kW

General technical specifications

Resistance	72 Ω
------------	------

Mechanical data

Degree of protection	IP65
Net weight	5.47 kg (12.06 lb)
Dimensions	
Width	349 mm (13.74 in)
Height	245 mm (9.65 in)
Depth	96.5 mm (3.80 in)

Standards

Compliance with standards	CE, UR, cURus
---------------------------	---------------

Connections

Power connection	
Version	shielded lead
Cable length	1.8 m (5.91 ft)

Environmental conditions

Cooling method	natural convection
Ambient temperature in operation	-30 ... 55 °C (-22 ... 131 °F)