



Figure similar

SIPLUS IPC 227E ET based on 6ES7647-8BE72-7HA1 with conformal coating, -25...+60 °C, 1x display port; 2x 10/100/1000 Mbps Ethernet RJ45; 1x USB3.0, 3x USB2.0; CFast slot; 24 V DC industrial power supply Celeron E3845 ET (4C/4T) with TPM (not for China); 4 GB ET with NVRAM; box: basic with COM 1/2; Windows 10 IoT Enterprise LTSB 2016, 64-bit, MUI (en, de, fr, it, es) 60 GB SSD ET, not exchangeable without SIMATIC software

General information	
Product type designation	IPC227E
Supply voltage	
Type of supply voltage	24 V DC
Processor	
Processor type	Intel Atom E3845
Drives	
SSD	Yes
Memory	
Capacity of main memory, max.	4 Gbyte
Hardware configuration	
Slots	
• Number of PCI slots	0
Interfaces	
Number of industrial Ethernet interfaces	2; 2x Ethernet (RJ45)
Number of PROFINET interfaces	1
Degree and class of protection	
IP degree of protection	IP40
Ambient conditions	
Ambient temperature during operation	
• min.	-20 °C
• max.	60 °C
Operating systems	
pre-installed operating system	Windows 10 IoT Enterprise 2016 LTSP, 64bit, MUI
Dimensions	
Width	191 mm
Height	100 mm
Depth	60 mm

last modified: 7/9/2022 