



SIMATIC DP, power supply module 24 V DC for ET200iSP, Ex db eb [ib] IIC T4
Gb, Ex db eb [ib] I Mb

Supply voltage	
Rated value (DC)	24 V
Reverse polarity protection	Yes
Input current	
from supply voltage L+, max.	4 A
Power loss	
Power loss, typ.	20 W
Interrupts/diagnostics/status information	
Status indicator	Yes
Alarms	No
Diagnoses	
• Diagnostic information readable	Yes; via IM 152
Diagnostics indication LED	
• Group error SF (red)	No
Potential separation	
primary/secondary	Yes
between supply voltage and electronics	Yes
Standards, approvals, certificates	
CE mark	Yes
Use in hazardous areas	
• ATEX marking	Ex de [ib]IIC T4
Dimensions	
Width	60 mm
Height	190 mm
Depth	136.5 mm
Weights	
Weight, approx.	2 700 g

last modified: 9/15/2021