
SIEMENS

Data sheet

6ES7655-5PX31-1AX0





General information	
Product type designation	DIQ Bundle
Engineering with	
 STEP 7 TIA Portal configurable/integrated from version 	V17
 STEP 7 configurable/integrated from version 	V5.6 HF2 and higher
 PCS 7 configurable/integrated from version 	V9.0 SP2 and higher
 PCS neo can be configured/integrated from version 	V3.1
 PROFINET from GSD version/GSD revision 	GSDML V2.3
Installation type/mounting	
Mounting position	Horizontal, vertical
Recommended mounting position	horizontal set up
Degree and class of protection	
IP degree of protection	IP66
Ambient conditions	
Ambient temperature during operation	
 horizontal installation, min. 	-40 °C
 horizontal installation, max. 	60 °C; Max. 4 A load current; up to 50 °C max. 5 A load current
 vertical installation, min. 	-40 °C
vertical installation, max.	50 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Dimensions	
Width	414 mm
Height	266 mm
Depth	111 mm
Weights	
Weight, approx.	5.5 kg

last modified:

9/2/2021