



SIMATIC ET 200SP HA, bus adapter BA 2XFC, 2x Fast Connect connection for PROFINET

General information	
Product type designation	BA 2xFC
Interfaces	
Number of PROFINET interfaces	1; 2 ports (switch) FC
Supports protocol for PROFINET IO	
• Number of FC (FastConnect) connections	2
Cable length	
— Cu conductors	100 m
Ambient conditions	
Ambient temperature during operation	
• min.	-40 °C
• max.	70 °C
• horizontal installation, min.	-40 °C
• horizontal installation, max.	70 °C
• vertical installation, min.	-40 °C
• vertical installation, max.	60 °C
Dimensions	
Width	20 mm
Height	69.5 mm
Depth	59 mm
Weights	
Weight, approx.	53 g

last modified: 6/29/2022 