



SIMATIC ET 200SP HA, bus adapter BA 2XLC 2 x LC glass FOC connections, for PROFINET

General information	
Product type designation	BA 2xLC
Interfaces	
Number of PROFINET interfaces	1; 2 ports (switch) LC Multimode Glass Fibre
Supports protocol for PROFINET IO	
• Number of LC ports	2
Cable length	
— Multimode graded-index fiber 50/125 µm	3 km
— Multimode graded-index fiber 62.5/125 µm	3 km
Ambient conditions	
Ambient temperature during operation	
• min.	-40 °C
• max.	65 °C; redundant design (2x 6DL1155-6AU00-0PM0): max. 60 °C horizontal, max. 50 °C vertical. When using different I/O devices, the derating specified there must be observed
• horizontal installation, min.	-40 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-40 °C
• vertical installation, max.	50 °C
Dimensions	
Width	20 mm
Height	75 mm; Without protective caps (approx. 8 mm)
Depth	59 mm
Weights	
Weight, approx.	60 g

last modified: 6/29/2022 