

Protective cover for MP 277 8" Touch to product version "ES 14" with narrow frame
Quantity: see technical data



General information	
Product type designation	Protective cover MP277 8" touch
Installation type/mounting	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
Degree and class of protection	
IP (at the front)	IP65
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature during operation	
• min.	-40 °C
• max.	80 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	80 °C
Relative humidity	
• Operation, max.	95 %
Mechanics/material	
Material	
• Plastic	Yes
Dimensions	
Width	270.8 mm
Height	211 mm
Thickness	7.8 mm
Mounting cutout, width	226 mm
Mounting cutout, height	166 mm
Weights	
Weight (without packaging)	750 g
Scope of supply	
Delivery quantity in pieces	
• Parts per unit	2; 2 cover frames, 2 base frames, 2 protective covers
Other	
Merchandise	No
Manufacturer name	SIEMENS AG
Manufacturer's address	Gleiwitzerstraße 555, 90475 Nuremberg, Germany
Target devices	For MP277 8" touch as far as product version "ES 14" with narrow frame
Usable in the following products	
• Product 1	6AV6643-0CB01-1AX0
last modified:	1/16/2021

