SIEMENS

## Data sheet 6AV6671-5CA00-0AX1

Service set mob. Panel Wirel. V1 Service set for Service set V1 Further information, Quantity and content: see technical data



| | |
|---|---|
| **General information** | |
| Product type designation | Service set Mobile Panel 277 (F) IWLAN V1 |
| **Standards, approvals, certificates** | |
| CE mark | Yes |
| **Ambient conditions** | |
| Ambient temperature during operation | |
| ● min. | 0 °C |
| ● max. | 55 °C |
| Ambient temperature during storage/transportation | |
| ● min. | -20 °C |
| ● max. | 70 °C |
| Relative humidity | |
| ● Operation, max. | 95 % |
| **Scope of supply** | |
| Delivery quantity in pieces | |
| ● Parts per unit | 1; Content: 2x covers for charging station l/r, 1x connector for charging station, 2x corner seals l/r, 2x gasket corner seals, 4x decorative film corner seals l/r, 1x backup battery 3.6 V / 1.5 Ah including cover, 1x spare key for charging cradle |
| **Other** | |
| Merchandise | No |
| Manufacturer name | SIEMENS AG |
| Manufacturer's address | Gleiwitzerstraße 555, 90475 Nuremberg, Germany |
| Target devices | for Mobile Panel 277 IWLAN V1, Mobile Panel 277F IWLAN V1 |
| Usable in the following products | |
| ● Product 1 | 6AV6645-0DD01-0AX0 |
| ● Product 2 | 6AV6645-0DE01-0AX0 |
| ● Product 3 | 6AV6645-0DB01-0AX0 |
| ● Product 4 | 6AV6645-0DC01-0AX0 |

**last modified:** 12/16/2020


Subject to change without notice
© Copyright Siemens