



Mounting clip spring Thin Client IP65 mounting clip for SIMATIC Thin Client Further information, Quantity and content: see technical data Sheet thickness from 1 mm to 4 mm Quantity and content: see technical data

General information	
Product type designation	Mounting clip, spring
Installation type/mounting	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
Standards, approvals, certificates	
RoHS conformity	Yes
Ambient conditions	
Ambient temperature during operation	
• min.	-40 °C
• max.	80 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	80 °C
Relative humidity	
• Operation, max.	90 %
Mechanics/material	
Enclosure material (front)	
• Plastic	Yes; For 1 ... 4 mm sheet thickness
Dimensions	
Width	20 mm
Height	35 mm
Thickness	20 mm
Weights	
Weight (without packaging)	8 g; Per unit
Scope of supply	
Delivery quantity in pieces	6; Spring-loaded terminals
Other	
Merchandise	No
Manufacturer name	SIEMENS AG
Manufacturer's address	Gleiwitzerstraße 555, 90475 Nuremberg, Germany
Target devices	SIMATIC Thin Client
Note:	Function-compatible to article number 6AV6671-8XK00-0AX1
Usable in the following products	
• Product 1	6AV6646-0AA21-2AX0
• Product 2	6AV6646-0AB21-2AX0

last modified:

12/18/2020