

Tablet PC support with handle for easier handling. Further information, quantity and content: See technical data



Figure similar

General information	
Product type designation	Tablet PC holder with handle
Control elements	
Frame size/design	
• Exceptional	Yes; Optimized for tablet PC, ITP1000
Ergonomics	
• Trackball rest	No; Adjustable handle with hook-and-loop connection, any useful angle can be set
• Adjustable height	No
Installation type/mounting	
Mounting type	Real assembly with provided screws
Degree and class of protection	
IP (all-round)	none
Standards, approvals, certificates	
CE mark	No; No CE marking obligation
Ambient conditions	
Suited for indoor use	Yes
Suited for outdoor use	Yes
Ambient temperature during operation	
• min.	0 °C
• max.	50 °C
Operation (vertical installation)	
— For vertical installation, min.	0 °C
— For vertical installation, max.	50 °C
Operation (max. tilt angle)	
— At maximum tilt angle, min.	0 °C
— At maximum tilt angle, max.	50 °C
Operation (vertical installation, portrait format)	
— For vertical installation, min.	0 °C
— For vertical installation, max.	50 °C
Operation (max. tilt angle, portrait format)	
— At maximum tilt angle, min.	0 °C
— At maximum tilt angle, max.	50 °C
Ambient temperature during storage/transportation	
• min.	-10 °C
• max.	60 °C
Relative humidity	
• Operation, max.	90 %
Mechanics/material	

Torques/forces	
• Tightening torque, min.	1 N·m; Insufficient torque can lead to loosening of the screws
• Tightening torque, max.	1.5 N·m
Weights	
Weight (without packaging)	0.4 kg
Weight (with packaging)	0.53 kg
Scope of supply	
Delivery quantity in pieces	1; 1x mounting plate with 4 lugs, 1x handle with hook-and-loop pad, 4x M4 screws, 4x washers
Other	
Merchandise	Yes
Manufacturer name	ADVITEX GmbH
Manufacturer's address	Eisenbahnstraße 40, 75228 Ispringen, Germany
Target devices	suitable for all appropriate interfaces
Note:	Commodity, can be used for ITP1000
Usable in the following products	
• Product 1	6AV7880-*

last modified:

1/15/2021 