



Protective film 22" glass front, type 1, Reflection Shield Matte, Further information, Quantity and content: see technical data

General information	
Product type designation	Protective film, 22" glass front
Installation type/mounting	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
Standards, approvals, certificates	
CE mark	No; No CE marking obligation
REACH	Yes; Tested
RoHS conformity	Yes; unnecessary
Ambient conditions	
Suited for indoor use	Yes
Suited for outdoor use	No; possible under certain conditions
Ambient temperature during operation	
• min.	0 °C
• max.	55 °C
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	60 °C
Relative humidity	
• Operation, max.	50 %
Mechanics/material	
Material	Polyester with functional hard layer, dirt-repellant, URM55, silicone adhesive layer
• Plastic	Yes; Non-reflecting, matte, can be removed without residue, hard-coated, dirt-repellant
• PET	Yes; Non-antistatic, non-reflecting, scratch-resistant, can be removed without residue
Enclosure material (front)	Scratching hardness 2H, adhesive force 0.011 N/25 mm
Dimensions	
Width	521 mm
Height	323 mm
Thickness	0.225 mm; Corners radius 3.1 mm
Weights	
Weight (without packaging)	44 g; Per unit
Scope of supply	
Delivery quantity in pieces	5; Units per set
Components included	5x removers, 5x cleaning cloths, 5x spatulas for applying
Other	
printable with laser printer	No; suitable for screen printing or UV printing
Merchandise	Yes; URM55 reflection shield, matte
Manufacturer name	Bedifol GmbH

Manufacturer's address	Byk-Gulden-Straße 2 // F22, 78467 Constance, Germany
contacting the manufacturer	Phone +49 (7531) 12738 10, email: info@bedifol.com
Target devices	for 22" widescreen Flat Panels, can also be cut to size for smaller, glass front displays, not suitable for membrane fronts
Note:	Surface-adhesive film, can be trimmed, printable, observe target device manual before attaching, limited suitability for resistive touch systems

last modified:

7/28/2022 