



Figure similar

Mounting clip steel, Type 2, captive Further information, quantity and content: See technical data

| General information                               |                                                                          |
|---------------------------------------------------|--------------------------------------------------------------------------|
| Product type designation                          | Mounting clip, steel, type 2                                             |
| Installation type/mounting                        |                                                                          |
| Mounting in portrait format possible              | Yes                                                                      |
| Mounting in landscape format possible             | Yes                                                                      |
| Standards, approvals, certificates                |                                                                          |
| CE mark                                           | No; No CE marking obligation                                             |
| RoHS conformity                                   | Yes                                                                      |
| Use in hazardous areas                            |                                                                          |
| • ATEX Zone 2                                     | Yes; Always comply with the operating instructions of the target device. |
| • ATEX Zone 22                                    | Yes; Always comply with the operating instructions of the target device. |
| • IECEx Zone 2                                    | Yes; Always comply with the operating instructions of the target device. |
| • IECEx Zone 22                                   | Yes; Always comply with the operating instructions of the target device. |
| Ambient conditions                                |                                                                          |
| Suited for indoor use                             | Yes                                                                      |
| Suited for outdoor use                            | Yes; possible under certain conditions                                   |
| Ambient temperature during operation              |                                                                          |
| • min.                                            | -40 °C                                                                   |
| • max.                                            | 80 °C                                                                    |
| Ambient temperature during storage/transportation |                                                                          |
| • min.                                            | -40 °C                                                                   |
| • max.                                            | 80 °C                                                                    |
| Relative humidity                                 |                                                                          |
| • Operation, max.                                 | 90 %                                                                     |
| Mechanics/material                                |                                                                          |
| Material                                          |                                                                          |
| • Plastic                                         | Yes; Interlock                                                           |
| • Sheet steel                                     | Yes                                                                      |
| Screw type                                        | M4x30 round head screw                                                   |
| • Cross-tip                                       | Yes                                                                      |
| • 4.5 V                                           | Yes                                                                      |
| Dimensions                                        |                                                                          |
| Width                                             | 19 mm                                                                    |
| Height                                            | 11.3 mm; Without screw                                                   |
| Depth                                             | 15 mm                                                                    |
| Weights                                           |                                                                          |
| Weight (without packaging)                        | 8 g                                                                      |
| Scope of supply                                   |                                                                          |
| Delivery quantity in pieces                       | 20; Units per set                                                        |

| Other                            |                                                                                             |
|----------------------------------|---------------------------------------------------------------------------------------------|
| Merchandise                      | No                                                                                          |
| Manufacturer name                | SIEMENS AG                                                                                  |
| Manufacturer's address           | Gleiwitzerstraße 555, 90475 Nuremberg, Germany                                              |
| Target devices                   | Panel and IPC from 2019                                                                     |
| Usable in the following products |                                                                                             |
| • Product 1                      | <a href="#">6AV2127-1AB00-0LX0</a>                                                          |
| • Product 2                      | 6AV2128-3*                                                                                  |
| last modified:                   |                                                                                             |
|                                  | 8/24/2021  |