

Power supply unit, external, for Mobile Panel IWLAN US, incl. power supply cable for USA Further information, Quantity and content: see technical data



General information	
Product type designation	External power supply unit
Supply voltage	
Type of supply voltage	AC
Rated value (AC)	100 - 240 V AC
Input current	
Current consumption (rated value)	1.4 A; 50 - 60 Hz
output voltage / header	
Rated value (DC)	12 V
Output current	
Current output (rated value)	5 A
Power	
Emitted active power	60 W; max.
EMC	
Emission of radio interference acc. to EN 55 011	
<ul style="list-style-type: none"> Limit class A, for use in industrial areas 	Yes; EN61000-4-2,3,4,5,6,8,11 light industry level
Standards, approvals, certificates	
CE mark	Yes; UL 69950, TÜV EN 600950-1, BSMI CNS14336, CCC GB4942 approved
CCC	Yes
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> min. max. 	-10 °C 50 °C
Ambient temperature during storage/transportation	
<ul style="list-style-type: none"> min. max. 	-20 °C 85 °C
Relative humidity	
<ul style="list-style-type: none"> Operation, max. 	90 %
Cables	
Cable length	
<ul style="list-style-type: none"> Input side Output side 	3 m 0.9 m
Color of cable sheath	Black
connection method	
Connector type	Connector 5.5 mm jack (-) / 2.1 mm pin (+) 12 V DC
Mechanics/material	
Material	
<ul style="list-style-type: none"> Plastic 	Yes
Color	Black

Dimensions	
Width	125 mm
Height	50 mm
Thickness	31.5 mm
Weights	
Weight (without packaging)	540 g
Weight (with packaging)	725 g
Scope of supply	
Delivery quantity in pieces	1; Incl. AC and DC connecting cable
• Parts per unit	1; AC cable for US
Other	
Merchandise	Yes
Manufacturer name	SIEMENS AG
Manufacturer's address	Gleiwitzerstraße 555, 90475 Nuremberg, Germany
Target devices	for Mobile Panel IWLAN
Usable in the following products	
• Product 1	6AV6645-0DD01-0AX0
• Product 2	6AV6645-0DE01-0AX0
• Product 3	6AV6645-0DB01-0AX0
• Product 4	6AV6645-0DC01-0AX0
• Product 5	6AV6645-0DD01-0AX1
• Product 6	6AV6645-0DE01-0AX1
• Product 7	6AV6645-0EB01-0AX1
• Product 8	6AV6645-0EC01-0AX1

last modified:

11/3/2021 