

PS2 keyboard 19" INT, with trackball, removable keyboard for devices with corresponding interface Further information, Quantity and content: see technical data



Figure similar

General information	
Product type designation	PS/2 built-in keyboard INT
Control elements	
Keyboard fonts	
<ul style="list-style-type: none"> • Design • Keyboard assignment • Color of the buttons • Color of the key inscription • Key illumination • Function keys <ul style="list-style-type: none"> — Number of function keys — Programmable • Number pad • status LED displays <ul style="list-style-type: none"> — for number pad — for Shift keys 	Membrane keyboard B3F, 101/102 or 104/105 OMRON light gray Black No 12 Yes Yes; Free-standing Yes; Num, Caps and Scroll Yes Yes
Connection type	
<ul style="list-style-type: none"> • USB • PS/2 	Yes; With PS/2 USB adapter (not included in the scope of supply) Yes
Frame size/design	
<ul style="list-style-type: none"> • Standard • 19" keyboard 	Yes; For industrial applications Yes
Installation type/mounting	
Rack mounting	No
Front mounting	Yes
Wall mounting/direct mounting	No
Input current	
Current consumption (rated value)	35 mA; Typical
Battery	
Battery-operated	No; maintenance-free
EMC	
Emission of radio interference acc. to EN 55 011	
<ul style="list-style-type: none"> • Limit class A, for use in industrial areas 	Yes
Degree and class of protection	
IP (all-round)	IP65 when the ball is actuated; mouse only IP55
Splashproof	Yes
Standards, approvals, certificates	
CE mark	Yes
RoHS conformity	Yes

Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	40 °C
Ambient temperature during storage/transportation	
• min.	-10 °C
• max.	50 °C
Relative humidity	
• Operation, max.	90 %; no condensation
• Condensation permissible	No
Operating systems	
Runs under operating system	
• Windows CE	Yes
• Windows Vista	Yes
• Windows XP	Yes
• Windows 7	Yes
• Windows 10	Yes
Mechanics/material	
Material	
• Sheet steel	Yes
Enclosure material (front)	
• Plastic	Yes; AUTOTEX (R) V150
Service life	
• Number of operating cycles, keys	1 000 000; Operations (minimum)
Dimensions	
Width	482.6 mm
Height	38 mm
Depth	177.8 mm
Weights	
Weight (without packaging)	1 490 g
Weight (with packaging)	1 735 g
Scope of supply	
Delivery quantity in pieces	1; Built-in keyboard with stud bolts
Other	
Merchandise	Yes; TIPRO no. K-842 (K-642)
Manufacturer name	TIPRO Representative Office
Manufacturer's address	Vogelweg 20, 31785 Hameln, Germany
Target devices	Suitable for IPC and HMI devices with the corresponding interfaces (see manual)
Note:	Suitable PS/2 USB adapter (keyboard/mouse): 1x USB 1.1, plug A on 2x PS/2 sockets, 0.20 m, black; manufacturer: Renkforce; supply by Conrad Elektronik, order no.: 1360251 - 62
Usable in the following products	
• Product 1	6AV2124-0GC13-0AX0
• Product 2	6AV2124-0QC13-0AX0
last modified:	9/29/2021 