

LI2Y 2X0,75ST + 2X (2X0,34ST) -CY SPECIAL CABLE, WITH BLUE SHEATH CONNECTION OF JB JUNCTION AND DISTRIBUTION BOX IN AN AREA SUBJECT TO EXPLOSION HAZARDS AND IB INTERMEDIATE BOX FOR PERMANENT ON-SITE INSTALLATION; OCCASIONAL BENDING POSSIBLE, APPROX. 10.8 MM OUTER DIAMETER, AMBIENT TEMPERATURE -40 TO +80 CEL. CABLE CUT TO LENGTH, WITHOUT CONNECTOR.

Further information

Industry Online Support (Manuals, Catalogs, Certificates, FAQ, ...)

<https://support.industry.siemens.com/cs/products?mfn=ps&lc=en-WW>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>

